

WTFWO-3633-03

**\$229**



### Freshwater Outfit

A complete outfit for pond fish culture, ideal for freshwater analysis. Nine critical test factors can be determined on-site efficiently and accurately. Designed with field analysis as a priority; all reagents, components and accessories are arranged in pre-drilled ethafoam. Short form instructions are provided in a handy adhesive lid label for easy reading. Long form instruction booklet provides detailed instructions and test kit diagram. Unit is supplied complete with labware, accessories, sampling bottle, and reagents for 50 tests of each factor.

### Freshwater

Octa-Slide Comparator Tests		
Test	Method	Range (# Tests)
Ammonia nitrogen	Nessler	0.2 to 3.0 (50)
Nitrite nitrogen	Diazotization/coupling	0.05 to 0.8 (50)
pH	Wide range	5.0 to 10.0 (50)

Direct Reading Titrator Tests		
Test	Method	Range (# Tests)
Alkalinity (Total)	Neutralization	0 to 200 ppm (50)
Carbon dioxide	Neutralization	0 to 50 ppm (50)
Chloride	Argentometric	0 to 200ppm (50)
Dissolved oxygen	Azide modification of Winkler method	0 to 10 ppm (50)
Hardness (total)	Complexometric	0 to 200 ppm (50)

Temperature	
Armored Thermometer	-5 to 45°C

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
WTFWO-3633-03	\$229	Freshwater combination kit
R-WTFWO-3633-03	130	Reagent refill kit

*Kit contents vary. Each kit comes complete with everything necessary to perform the specified test.*

**Ordering Example:** WTFWO-3633-03, complete test kit for freshwater analysis, \$229.

G-45

For Sales & Service **1-800-82-66342**<sup>®</sup>  
**1-800-TC-OMEGA**  
 U.S.A. and Canada

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters