

CONDUCTIVE LEVEL CONTROLLERS

LVCN4000 Series
Starts at

\$484




- ✓ Accurate and Reliable Measurement
- ✓ Easy Installation
- ✓ Rugged Construction
- ✓ No Moving Parts
- ✓ 100 to 2000 mm (0.33 to 6.5') Rod Lengths Available
- ✓ Rod Can be Cut in the Field
- ✓ ECTFE/ETFE Coating Available

The LVCN4000 Series conductive level switch controllers offer a wide range of customized options to meet any application's need. They are designed to control the level of all conductive media with up to 2 different points of level control.

The LVCN4100 Series has a single rod and is able to control one point of level. The LVCN4200 Series can accommodate up to 2 rods and is able to control 2 points of levels. Both models feature a 24 Vdc power supply and an internal relay that substitutes for an external relay. As with other conductive probes, the rods for these 2 models can be custom-cut and made with any process connection, such as threaded or sanitary. In addition, the electrodes operate on alternating current to prevent electrolyses.

LVCN4231-36-48-ETFE,
\$706, shown smaller
than actual size.

LVCN4121-48-ETFE,
\$484, shown smaller
than actual size.



SPECIFICATIONS

Power Supply: 24 Vdc ($\pm 10\%$)
Current Consumption: Max 2 VA
Temperature Range:
316 SS: -10 to 82°C (-14 to 180°F)
ETFE: -10 to 120°C (-14 to 248°F)
Max Pressure: 290 psi (20 bar)
Wetted Materials: 316 SS
Enclosure Material: Glass-filled nylon standard, aluminum optional

Electrical Connection:
 Cable entry and ½ NPT conduit
Process Connection:
 ½, ¾, 1, 1½ NPT; Tri-Grip™ (Tri-Clamp® compatible) or flange
Output: 5 A SPDT relay (250 Vac max)
Time Delay: 0.1 to 5 seconds nominal
Sensitivity Adjustment: 0.5 to 50 kΩ (potentiometer)

Electrodes: 316 SS
Electrode Length:
 100 to 2000 mm (3.9" to 6.5')
Output Voltage of Electrodes:
 12 V to 100 Hz
Weight: Approx. 2.7 kg (6 lb) for 1.2 m (4')
Protection Class: NEMA 4 (IP65)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description of Capacitance Transmitter with 4 to 20 mA Output Standard
LVCN4121-48-ETFE	\$484	1 rod, ¾ NPT, 48" L, ECTFE/ETFE coated, max temp 120°C (248°F), approx 680 g (1.5 lb)
LVCN4231-36-48-ETFE	706	2 rods, 1 NPT, 36" L rod and 48" L rod, ECTFE/ETFE coated, 120°C (248°F) approx 1.0 kg (2.3 lb)

Custom Models Available*

Model No.	Price	Description
LVCN41(A)(B)-(C)	\$222	Custom conductive level controller, single rod, select process connection (A), enclosure (B), and rod length in inches (C)
LVCN42(A)(B)-(C)	252	Custom conductive level controller, dual rod, select process connection (A), enclosure (B), and rod length in inches (C)

* Rods must be coated when using the probes above 82°C (180°F). All conductive applications must have a reference point, such as the metallic tank wall or another rod for non-metallic tanks.

Options

Ordering Suffix	Additional Price	Description
A-Process Connection		
1	N/C	½ NPT thread
2	N/C	¾ NPT thread
3	N/C	1 NPT thread
4	\$150	1½ NPT thread
5	150	1.5" Tri-Grip™, sanitary
6	300	2" flange, ANSI, 15016 316 SS
Others	Call for price	Consult Engineering with details
B-Enclosure		
1	\$6	Glass-filled nylon with ½ NPT conduit and cable gland
2	84	Aluminum die cast with ½ NPT conduit entry
3	90	Aluminum die cast with cable gland
C-Rod Length		
Specify INCHES	\$22/ft/rod	Rod length (in), 96" max
Other Options		
-ETFE	\$42/ft	ECTFE/ETFE probe coating

Comes complete with operator's manual.

Ordering Examples: LVCN4121-48-ETFE, 1-rod (48") level controller, PSU-93, unregulated power supply, 70A-1, alarm, \$484 + 40 + 18 = \$498.

LVCN4231-36-48-ETFE, 2-rod (36 to 48") level controller, \$706.

Accessories

Model No.	Price	Description
70A-1	\$18	Continuous tone alarm
TX4-100	35	30.5 m (100') spool of 4-conductor wire
PSU-93	40	Unregulated 24 Vdc power supply

Recommended Reference Book: Wastewater Treatment Biological and Chemical Processes, ES-2253, \$159. See Section Y for Additional Books.



LVCN4000 Series, shown smaller than actual size.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters